



uPM60V

Veterinary Pulse Oximeter

The uPM60V Veterinary Pulse Oximeter is a low cost monitor for spot checking, continuous, noninvasive monitoring or recording of functional oxygen saturation of arterial SpO₂, pulse rate and pulse strength. It may be used in the veterinary hospital or clinical environment. The oximeter works with given sensors providing SpO₂ and pulse rate on a variety of veterinaries like horses, dogs and cats etc with adjustable alarm limits as well as visible and audible alarm signals.

- 3.5" Large size color touch screen(optional), 320X480 pixels.
- Turn off automatically for power saving.
- Uses Lithium battery.
- Three measurement modes: spot-check, monitoring and record.
- Continuous storage of data for 999 patient data in 120 hours.
- Data can be stored on a computer and managed, analyzed and printed by using the ODMS system.
- Silent sleep monitoring, with data storage and automatic power-saving features for patients with 24 hours uninterrupted care.
- Expanded heart rate values and veterinary specific SpO₂ sensors to accommodate a variety of species.



SPECIFICATIONS

Enclosure

Weight	280g(0.617lb)with batteries
Dimensions	78.5mmWx158mmHx31.5mmD (3.09in.Wx6.22in.Hx1.24in.D)
Display	
Screen size	88.9mm(3.5'),measured diagonally
Screen type	TFT LCD, white LED backlight
Resolution	320x480pixels
Alarms	
Categories	Patient status and system status
Priorities	Low,medium,and high
Notification	Audible and visual
Setting	Fullstorage,low battery and sensor off
Alarm volume level	45 to 85 decibels
Alarmsystem delay	<10seconds

SpO2

Measurement range	1% to 100%
Accuracy	70-100% ($\pm 2\%$), <70% undefined
Resolution	1%
Display wave speed	10.00 mm/sec

Pulse Rate

PR range	30bpm to 400bpm
Accuracy	$\pm 2\text{bpm}/\pm 2\%$ take maximum
Resolution	1bpm

Electrical

Battery	Lithium battery with 4,400mAh will typically provide 15 hours of monitoring with no external communication, no audible alarm sound.
Type	Lithium Battery
Voltage	3.7V

Environmental

Transport and Storage		Operating Conditions
Temperature	(- 20 ~ + 55) °C (- 4 ~ + 131) °F	(+ 5 ~ + 40) °C (+ 41 ~ + 104) °F
Atmospheric Pressure	700hPa to 1060hPa	
Relative humidity	15% to 95% non condensing	

Configuration

Standard	Main unit, Veterinary SpO2 sensor, Charging base, Lithium Battery
Optional Configuration	Data Analysis Software(ODMS), Touch Screen

Trend

Tabular	
Memory	Saves a total of 120hours of data events; saves date and time, alarm conditions, measurements
Tabular format	One table for all parameters

ACCESSORIES



Vet Lingual Clip SpO2 Sensor



AC Adapter



Data Analysis Software

UTECH CO., LTD.

Add. : UTMI Building, No.390, Jingdongfang Avenue, Beibei District, Chongqing, 400715, P. R. China.

Eml. : service@chinautech.com

Web : www.chinautech.com

Tel : +86-23-86082658

Fax : +86-23-86082218

This brochure is for reference only and subject to change without notice.
This brochure covers copyrighted images owned by UTECH.

